NI 6703/6704 Specifications

This document lists specifications for the NI PCI-6703 and NI PCI/PXI-6704. These specifications are valid for an ambient temperature of 0 to 55 °C, unless otherwise noted.

Analog Output

Number of voltage channels 16	
Number of current channels (NI 6704 only)16	
Resolution 16-bit	
Recommended warm-up time 15 minutes	

Transfer Characteristics

INL	±1 LSB max
DNL	±1 LSB max
Monotonicity	16 bits, guaranteed

Voltage Output

Output coupling	DC
Output impedance	0.1 Ω max
Current drive	±10 m ∧ may

Range ±10.1 V

Load capacitance	10,000 pF max
Protection	Short-circuit to ground
Noise	100 μV_{rms} , DC to 1 MHz
Power-on state	Independent, user-defined values

Current Output (NI 6704 Only)

ourront output (in oron t	···· <i>y </i>
Range	0.1 to 20.2 mA
Type	Source, does not require external excitation source
Output impedance	1 GΩ min
Output compliance	0 to 10 V, not clamped
Noise	1 µA _{rms} , DC to 1 MHz
Protection	Short-circuit and open circuit
Power-up state	Independent, user-defined values

Accuracy Information

		Absolute Accuracy				Absolute Accuracy	Accuracy	
Output	Nominal Range at	% of Reading				Temp Drift	at Full Scale	
Туре	Full Scale	24 Hours	90 Days	1 Year	Offset	(%/°C)	24 Hours	1 Year
Voltage	±10.1 V	0.0019%	0.0026%	0.0035%	±710 μV	0.0001%	0.91 mV	1.07 mV
Current*	0.1–20.2 mA	0.0034%	0.0088%	0.0150%	±1,435.0 nA	0.0002%	2.16 μΑ	4.48 μΑ

 $\label{eq:Note:equality} \textbf{Note} : \text{Temp drift applies only if ambient is greater than ± 10 °C of previous external calibration. Absolute Accuracy at Full Scale calculations assume full scale output.}$

* NI 6704 only



Dynamic Characteristics

Settling time (including channel latency)

Accuracy	Time
±0.1%	1.8 ms typ, 5.6 ms max
±0.01%	3.6 ms typ, 11.2 ms max
±0.001%	14.4 ms typ, 48.8 ms max

Stability

Offset temperature coefficient Voltage......5 μV/°C Current (NI 6704 only)10 nA/ °C Gain temperature coefficient Voltage......1 ppm/°C Current (NI 6704 only)2 ppm/°C

Digital I/O

Number of channels.....8 Compatibility.....TTL Power-on stateInput (high impedance) Digital logic levels

Level	Min	Max
Input low voltage	_	0.8 V
Input high voltage	2.0 V	_
Output low voltage	_	$0.55 \text{ V}, I_{OL} = 16 \text{ mA}$
Output high voltage	$2.4 \text{ V}, I_{OH} = 16 \text{ mA}$	_
Input leakage current	_	10 μΑ

Bus Interface

٦	Cyne	Slava

Power Requirement

NI 6703...... 1.5 A NI 6704......2.6 A +12 V 70 mA



Note These power usage figures do not include the power used by external devices that are connected to the fused supply present on the I/O connector. They assume that all voltage and current outputs are fully loaded.

Power available at I/O connector.... +4.5 to +5.25 VDC at 0.75 A

Physical

Dimensions (not including connectors) NI PCI-6703/6704 9.9 × 17.5 cm $(3.9 \times 6.9 \text{ in.})$ NI PXI-6704..... 10 × 16 cm $(3.9 \times 6.3 \text{ in.})$

I/O connector 68-pin male

Maximum Working Voltage

Maximum working voltage refers to the signal voltage plus the common-mode voltage.

Category I

Measurement Category I is for measurements performed on circuits not directly connected to the electrical distribution system referred to as MAINS voltage. This category is for measurements of voltages from specially protected secondary circuits. Such voltage measurements include signal levels, special equipment, limited-energy parts of equipment, circuits powered by regulated low-voltage sources, and electronics.



Caution Do *not* use this device for connection to signals or for measurements within Measurement Categories II, III, or IV.

NI 6703/6704 Specifications 2 ni.com

¹ NI PXI-6704 devices do not use power from the -12 V rail.

Environmental

Maximum altitude......2,000 m

Pollution Degree2



Note Clean the device with a soft, non-metallic brush. Make sure that the device is completely dry and free from contaminants before returning it to service.

Safety

This product is designed to meet the requirements of the following standards of safety for electrical equipment for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA 61010-1



Note For UL and other safety certifications, refer to the product label or the *Online Product Certification* section.

Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326 (IEC 61326): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- AS/NZS CISPR 11: Group 1, Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



Note For the standards applied to assess the EMC of this product, refer to the *Online Product Certification* section.



Note For EMC compliance, operate this device with shielded cables.

CE Compliance $\subset \in$

This product meets the essential requirements of applicable European Directives as follows:

- 2006/95/EC; Low-Voltage Directive (safety)
- 2004/108/EC; Electromagnetic Compatibility Directive (EMC)

Online Product Certification

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for this product, visit ni.com/certification, search by model number or product line, and click the appropriate link in the Certification column.

Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the *NI* and the Environment Web page at ni.com/environment. This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

Waste Electrical and Electronic Equipment (WEEE)



EU Customers At the end of the product life cycle, all products *must* be sent to a WEEE recycling center. For more information about WEEE recycling centers, National Instruments WEEE initiatives, and compliance with WEEE Directive 2002/96/EC on Waste and Electronic Equipment, visit ni.com/environment/weee.

电子信息产品污染控制管理办法 (中国 RoHS)



中国客户 National Instruments 符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于National Instruments 中国 RoHS 合规性信息,请登录 ni.com/environment/rohs_china。(For information about China RoHS compliance, go to ni.com/environment/rohs_china.)

Device Pinouts

AO 0 (V)	34	68	AO GND 0
AO GND 1	33	67	NC
NC	32	66	AO 1 (V)
AO 2 (V)	31	65	AO GND 2
AO GND 3	30	64	NC
NC	29	63	AO 3 (V)
AO 4 (V)	28	62	AO GND 4
AO GND 5	27	61	NC
NC	26	60	AO 5 (V)
A0 6 (V)	25	59	AO GND 6
AO GND 7	24	58	NC
NC	23	57	AO 7 (V)
AO 8 (V)	22	56	AO GND ¹
NC	21	55	AO GND 8
AO GND 9	20	54	AO 9 (V)
AO GND ¹	19	53	NC
AO GND 10	18	52	AO 10 (V)
AO 11 (V)	17	51	NC
NC	16	50	AO GND 11
AO 12 (V)	15	49	AO GND 12
AO GND 13	14	48	NC
NC	13	47	AO 13 (V)
AO 14 (V)	12	46	AO GND 14
AO GND 15	11	45	NC
NC	10	44	AO 15 (V)
P0.7	9	43	AO GND ¹
P0.6	8	42	D GND
P0.5	7	41	D GND
P0.4	6	40	RESERVED
P0.3	5	39	D GND
P0.2	4	38	RESERVED
P0.1	3	37	D GND
P0.0	2	36	D GND
+5 V	1	35	D GND ¹
			•

V = Voltage I = Current NC = No Connect

1 No Connect when using the SH68-68-D1 cable.

Figure 3. NI 6703 Connector Pin Assignments

(
AO 0 (V)	34	68	AO GND 0/16
AO GND 1/17	33	67	AO 16 (I)
AO 17 (I)	32	66	AO 1 (V)
AO 2 (V)	31	65	AO GND 2/18
AO GND 3/19	30	64	AO 18 (I)
AO 19 (I)	29	63	AO 3 (V)
AO 4 (V)	28	62	AO GND 4/20
AO GND 5/21	27	61	AO 20 (I)
AO 21 (I)	26	60	AO 5 (V)
A0 6 (V)	25	59	AO GND 6/22
AO GND 7/23	24	58	AO 22 (I)
AO 23 (I)	23	57	AO 7 (V)
AO 8 (V)	22	56	AO GND ¹
AO 24 (I)	21	55	AO GND 8/24
AO GND 9/25	20	54	AO 9 (V)
AO GND ¹	19	53	AO 25 (I)
AO GND 10/26	18	52	AO 10 (V)
AO 11 (V)	17	51	AO 26 (I)
AO 27 (I)	16	50	AO GND 11/27
AO 12 (V)	15	49	AO GND 12/28
AO GND 13/29	14	48	AO 28 (I)
AO 29 (I)	13	47	AO 13 (V)
AO 14 (V)	12	46	AO GND 14/30
AO GND 15/31	11	45	AO 30 (I)
AO 31 (I)	10	44	AO 15 (V)
P0.7	9	43	AO GND ¹
P0.6	8	42	D GND
P0.5	7	41	D GND
P0.4	6	40	RESERVED
P0.3	5	39	D GND
P0.2	4	38	RESERVED
P0.1	3	37	D GND
P0.0	2	36	D GND
+5 V	1	35	D GND ¹
	۰ .	\mathcal{I}	

V = Voltage I = Current NC = No Connect

1 No Connect when using the SH68-68-D1 cable.

Figure 4. NI 6704 Connector Pin Assignments

LabVIEW, National Instruments, NI, ni.com, the National Instruments corporate logo, and the Eagle logo are trademarks of National Instruments Corporation. Refer to the *Trademark* Information* at ni.com/trademarks for other National Instruments trademarks. Other product and company names mentioned herein are trademarks or trade names of their respective companies. For patents covering National Instruments products/technology, refer to the appropriate location: *Help*Patents* in your software, the patents.txt file on your media, or the *National Instruments Patent Notice* at ni.com/patents. Refer to the *Export Compliance Information* at ni.com/legal/export-compliance for the National Instruments global trade compliance policy and how to obtain relevant HTS codes, ECCNs, and other import/export data.